



External micrometer, Measuring range: 25-50mm



Order data

Order number	420200 25-50
GTIN	4045197203779
Item class	42B

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

Supplied with:

From size 25-50 including 1 setting standard.

Packaging: sturdy box

Standard: DIN 863

Micrometer barrel graduations: 1/50 mm

Calibration: B1

Calibration: B2

Scale divisions: 0.01 mm

Error limit: 2 μ m

Spindle \varnothing : 6.5 mm

Barrel \varnothing : 18 mm

Technical description

Barrel \varnothing	18 mm
Scale divisions	0.01 mm
Spindle \varnothing	6.5 mm

Measuring range	25 - 50 mm
Micrometer barrel graduations	1/50 mm
Calibration	B1
Calibration	B2
Error limit	2 µm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External tube micrometer maximum measuring range 100 mm	012050 100
Calibration Micrometer standard for external micrometer maximum nominal size 100 mm	012110 100
Labelling laser-etched Type	018940
DAkkS calibration External micrometer maximum measuring range 100 mm	012060 100
Calibration External tube micrometer maximum measuring range 100 mm	022000 100
Calibration Micrometer standard for external micrometer maximum nominal size 100 mm	022080 100
DAkkS calibration External micrometer maximum measuring range 100 mm	022010 100
100	022090 100

Accessories

Micrometer setting standard overall length 25 mm	421100 25
--	-----------