



## External micrometer, Measuring range: 50-75mm



### Order data

Order number	420410 50-75
GTIN	4059192003661
Item class	43A

### Description

#### Version:

#### Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

#### Supplied with:

From size 25-50 including 1 setting standard.

### Technical description

Measuring range	50 - 75 mm
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Barrel Ø	17.5 mm
Spindle Ø	6.5 mm
Calibration	B2
Error limit	5 µm
Standard	Works standard
Ratchet	yes

Hand temperature protection	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

### **Suitable products**

<https://www.hoffmann-group.com/GB/en/hom/p/420410-50-75>