

Mitutoyo
External micrometer, Measuring range: 50-75mm

Order data

Order number	420500 50-75
GTIN	4946368385648
Item class	44A

Description
Version:
Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

From size 100-125, enamelled cast frame.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Barrel Ø	18 mm
Type of measurement face	Carbide tipped
Micrometer barrel graduations	1/50 mm
Spindle Ø	6.35 mm
Scale divisions	0.01 mm
Spindle pitch	1/50 mm
Measuring range	50 - 75 mm
Calibration	B2

Error limit	2 µm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

Accessories

Micrometer setting standard overall length 50 mm	421100 50
--	-----------