

Mitutoyo
External micrometer, Measuring range: 25-50mm

Order data

Order number	420540 25-50
GTIN	4946368543376
Item class	44A

Description
Version:
Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle. Locking by clamping lever.

With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.

With clearly engraved, black divisions and numerals.

With combined sensitive ratchet for one-hand operation and operation within the bracket.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Weight	0.4 kg
Barrel Ø	18 mm
Type of measurement face	Carbide tipped
Spindle Ø	6.35 mm
Micrometer barrel graduations	1/50 mm
Measuring range	25 - 50 mm
Scale divisions	0.01 mm
Calibration	B2
Error limit	2 µm

Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Micrometer setting standard overall length 25 mm	421100 25
--	-----------