

## Edge finder, Contact point Ø: 10/4mm



### Order data

Order number	359000 10/4
GTIN	4045197350244
Item class	38D

### Description

#### Version:

The contact point has a flexible connection to the body via a spring, with an **alignment accuracy of 0.01 mm.**

All parts fully hardened and ground. With stepped contact point 10 and 4 mm Ø.

#### Version of the advertising text:

**Alignment accuracy 0.01 mm.**

#### Application:

For alignment of component reference surfaces or edges.

Spindle speed approx. 600 rpm.

#### Use of the advertising text:

For alignment of component reference surfaces or edges. Spindle speed approx. 600 rpm.

### Technical description

Tool shank Ø	10 mm
Contact point Ø	10 mm
Overall length	90 mm
Type of product	Probes

---

## Accessories

Spare spring for edge finder Ø×Overall length 2,6X25 mm	359010 2,6X25
Spare spring for edge finder Ø×Overall length 4,6X40 mm	359010 4,6X40