



## External micrometer, Measuring range: 50-75 mm



### Order data

Order number	420200 50-75
GTIN	4045197203786
Item class	42B

### Description

#### Version:

#### Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

#### Supplied with:

From size 25-50 including 1 setting standard.

Packaging: sturdy box

Standard: DIN 863

Micrometer barrel graduations: 1/50 mm

Calibration: B1

Calibration: B2

Scale divisions: 0.01 mm

Error limit: 2  $\mu$ m

Spindle  $\varnothing$ : 6.5 mm

Barrel  $\varnothing$ : 18 mm

### Technical description

Micrometer barrel graduations	1/50 mm
Measuring range	50 - 75 mm
Scale divisions	0.01 mm

Spindle Ø	6.5 mm
Barrel Ø	18 mm
Calibration	B1
Calibration	B2
Error limit	2 µm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

## Services

CalibrationMicrometer standard for external micrometer maximum nominal size 100 mm	012110 100
Labellinglaser-etched Type	018940
DAkkS calibrationExternal micrometer maximum measuring range 100 mm	022010 100
CalibrationExternal tube micrometer maximum measuring range 100 mm	022000 100
CalibrationMicrometer standard for external micrometer maximum nominal size 100 mm	022080 100

## Accessories

Micrometer setting standard overall length 50 mm	421100 50
--	-----------