

 Mahr**External micrometer, Measuring range: 75-100mm****Order data**

Order number	420410 75-100
GTIN	4059192003678
Item class	43A

Description**Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Micrometer barrel graduations	1/50 mm
Spindle Ø	6.5 mm
Scale divisions	0.01 mm
Barrel Ø	17.5 mm
Measuring range	75 - 100 mm
Calibration	B2
Error limit	5 µm
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

Accessories

Micrometer setting standard overall length 75 mm	421100 75
--	-----------