

**Mitutoyo****External micrometer, Measuring range: 0-25mm****Order data**

Order number	420545 0-25
GTIN	4946368508542
Item class	44A

**Description****Version:**

**Precision lapped, carbide-tipped measuring faces.** Hardened and ground measuring spindle. Locking by locking lever. With ratchet and hand temperature protection. Barrel non-reflecting chromium plated. Clearly engraved black divisions and numerals. With combined ratchet for **one-hand operation** and operation in the bracket. **Reading 0.001 mm.**

Packaging: sturdy box

Standard: DIN 863

Micrometer barrel graduations: 1/50 mm

Calibration: B1

Scale divisions: 0.001 mm

Error limit: 2 µm

Spindle Ø: 6.35 mm

Barrel Ø: 18 mm

Weight: 0.3 kg

**Technical description**

Scale divisions	0.001 mm
Spindle Ø	6.35 mm
Weight	0.3 kg
Barrel Ø	18 mm

Type of measurement face	carbide tipped
Micrometer barrel graduations	1/50 mm
Measuring range	0 - 25 mm
Calibration	B1
Error limit	2 µm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

## Services

Calibration External tube micrometer maximum measuring range 25 mm	012050 25
Labelling laser-etched Type	018940
DAkkS calibration External micrometer maximum measuring range 100 mm	012060 100
DAkkS calibration External micrometer maximum measuring range 100 mm	022010 100
Calibration External tube micrometer maximum measuring range 25 mm	022000 25