

Garant**External micrometer, Measuring range: 100-125mm****Order data**

Order number	420402 100-125
GTIN	4045197471581
Item class	41B

Description**Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle. Locking by clamping lever.

With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.

With clearly engraved, black divisions and numerals.

With combined sensitive ratchet for one-hand operation and operation within the bracket.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Number of micrometer standards	1
Scale divisions	0.01 mm
Spindle Ø	6.5 mm
Measuring range	100 - 125 mm
Micrometer barrel graduations	1/50 mm
Barrel Ø	19 mm
Calibration	B2
Standard	DIN 863

Ratchet	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 200 mm	022050 200
Calibration External micrometer including setting dimension maximum measuring range 200 mm	022040 200

Accessories

Micrometer setting standard overall length 100 mm	421100 100
---------------------------------------------------	------------