



Tee bolt (12.9.) single, Type: 141250



Order data

Order number	375310 141250
GTIN	4020772086183
Item class	35A

Description

Version:

T-bolt, forged and rolled thread.

High-tensile design, strength class = 12.9.

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

Nut width e	22 mm
narrow nut width a	13.7 mm
Thread length b	35 mm
Height k	8 mm
T-slot nominal size	14 mm
Thread G	M12
Length L	50 mm
Type	787
Type of product	Tee-bolt

