

**External micrometer 1/100 graduations, Measuring range: 0-25mm****Order data**

Order number	420750 0-25
GTIN	4045197203854
Item class	42B

**Description****Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle; with locking lever

With ratchet and hand temperature protection.

**Supplied with:**

From size 25 – 50 supplied with 1 setting standard.

**Technical description**

Measuring range	0 - 25 mm
Micrometer barrel graduations	1/100 mm
Scale divisions	0.01 mm
Spindle Ø	8 mm
Barrel Ø	30 mm
Calibration	B1
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

---

## Services

Calibration External micrometer without setting dimension  
maximum measuring range 25 mm

022000 25