



External micrometer, Measuring range: 75-100 mm



Order data

Order number	420200 75-100
GTIN	4045197203793
Item class	42B

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

Supplied with:

From size 25-50 including 1 setting standard.

Packaging: sturdy box

Standard: DIN 863

Micrometer barrel graduations: 1/50 mm

Calibration: B1

Calibration: B2

Scale divisions: 0.01 mm

Error limit: 3 μ m

Spindle \varnothing : 6.5 mm

Barrel \varnothing : 18 mm

Technical description

Measuring range	75 - 100 mm
Spindle \varnothing	6.5 mm
Micrometer barrel graduations	1/50 mm

Scale divisions	0.01 mm
Barrel Ø	18 mm
Calibration	B1
Calibration	B2
Error limit	3 µm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

CalibrationMicrometer standard for external micrometer maximum nominal size 100 mm	012110 100
Labellinglaser-etched Type	018940
CalibrationMicrometer standard for external micrometer maximum nominal size 100 mm	022080 100
DAkkS calibrationExternal micrometer maximum measuring range 100 mm	022010 100
CalibrationExternal tube micrometer maximum measuring range 100 mm	022000 100

Accessories

Micrometer setting standard overall length 75 mm	421100 75
--	-----------