



## Tee bolt (12.9.) single, Type: 101040



### Order data

Order number	375310 101040
GTIN	4020772083953
Item class	35A

### Description

**Version:**

T-bolt, forged and rolled thread.

**High-tensile design**, strength class = 12.9.

**Standard:**

**DIN 787**

**Supplied with:**

**Single**, without nut and washer.

**Optional extras:**

Washers, see No. 375340 and tall nuts, see No. 375385.

**Note:**

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

### Technical description

T-slot nominal size	10 mm
Height k	6 mm
narrow nut width a	9.7 mm
Thread length b	30 mm
Nut width e	15 mm
Thread G	M10
Length L	40 mm
Type	787
Type of product	Tee-bolt

