



## External micrometer, Measuring range: 100-125mm



### Order data

Order number	420410 100-125
GTIN	4059192003685
Item class	43A

### Description

#### Version:

#### Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

#### Supplied with:

From size 25-50 including 1 setting standard.

### Technical description

Scale divisions	0.01 mm
Barrel Ø	17.5 mm
Micrometer barrel graduations	1/50 mm
Spindle Ø	6.5 mm
Measuring range	100 - 125 mm
Calibration	B2
Error limit	6 µm
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

### Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 200 mm	022050 200
Calibration External micrometer including setting dimension maximum measuring range 200 mm	022040 200

### Accessories

Micrometer setting standard overall length 100 mm	421100 100
---	------------