

Garant**External micrometer, Measuring range: 125-150mm****Order data**

Order number	420402 125-150
GTIN	4045197471598
Item class	41B

Description**Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle. Locking by clamping lever.

With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.

With clearly engraved, black divisions and numerals.

With combined sensitive ratchet for one-hand operation and operation within the bracket.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Measuring range	125 - 150 mm
Micrometer barrel graduations	1/50 mm
Barrel Ø	19 mm
Scale divisions	0.01 mm
Spindle Ø	6.5 mm
Number of micrometer standards	1
Calibration	B2
Standard	DIN 863

Ratchet	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 200 mm	022040 200
DAkkS calibration External micrometer including setting dimension maximum measuring range 200 mm	022050 200