



External micrometer 1/100 graduations, Measuring range: 25-50mm



Order data

Order number	420750 25-50
GTIN	4045197203861
Item class	42B

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle; with locking lever

With ratchet and hand temperature protection.

Supplied with:

From size 25 – 50 supplied with 1 setting standard.

Technical description

Barrel Ø	30 mm
Scale divisions	0.01 mm
Micrometer barrel graduations	1/100 mm
Spindle Ø	8 mm
Measuring range	25 - 50 mm
Calibration	B2
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting
dimension maximum measuring range 100 mm

022050 100

Calibration External micrometer including setting
dimension maximum measuring range 100 mm

022040 100

Accessories

Micrometer setting standard overall length 25 mm

421100 25