

Mitutoyo
External micrometer, Measuring range: 125-150mm

Order data

| | |
|--------------|----------------|
| Order number | 420500 125-150 |
| GTIN | 4946368214986 |
| Item class | 44A |

Description
Version:
Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

From size 100-125, enamelled cast frame.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

| | |
|-------------------------------|----------------|
| Scale divisions | 0.01 mm |
| Micrometer barrel graduations | 1/50 mm |
| Type of measurement face | Carbide tipped |
| Spindle pitch | 1/50 mm |
| Spindle Ø | 6.35 mm |
| Measuring range | 125 - 150 mm |
| Barrel Ø | 18 mm |
| Calibration | B2 |

| | |
|------------------------|--------------------------|
| Error limit | 3 µm |
| Standard | DIN 863 |
| Measurement technology | analogue |
| Packaging | sturdy box |
| Type of product | External tube micrometer |

Services

| | |
|--|------------|
| DAkkS calibration External micrometer including setting dimension maximum measuring range 200 mm | 022050 200 |
| Calibration External micrometer including setting dimension maximum measuring range 200 mm | 022040 200 |