



Tee bolt (10.9. / 8.8.) single, Type: 1614125



Order data

Order number	375305 1614125
GTIN	4020772084431
Item class	35A

Description

Version:

T-bolt, forged and rolled thread.

Standard design, strength class = 10.9 (for M6 – M12) and strength class = 8.8 (for M14 – M24).

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

narrow nut width a	15.7 mm
Height k	9 mm
T-slot nominal size	16 mm
Thread length b	75 mm
Nut width e	25 mm
Thread G	M14
Length L	125 mm
Type	787
Type of product	Tee-bolt

