



External micrometer, Measuring range: 125-150mm



Order data

Order number	420410 125-150
GTIN	2050001053114
Item class	43A

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Spindle Ø	6.5 mm
Barrel Ø	17.5 mm
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Measuring range	125 - 150 mm
Calibration	B2
Error limit	6 µm
Standard	DIN 863
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 200 mm	022050 200
Calibration External micrometer including setting dimension maximum measuring range 200 mm	022040 200