



## Tee bolt (12.9.) single, Type: 1010100



### Order data

Order number	375310 1010100
GTIN	4020772083922
Item class	35A

### Description

#### Version:

T-bolt, forged and rolled thread.

**High-tensile design**, strength class = 12.9.

#### Standard:

**DIN 787**

#### Supplied with:

**Single**, without nut and washer.

#### Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

#### Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

### Technical description

Height k	6 mm
Thread length b	60 mm
T-slot nominal size	10 mm
narrow nut width a	9.7 mm
Nut width e	15 mm
Thread G	M10
Length L	100 mm
Type	787
Type of product	Tee-bolt

