



## External micrometer, Measuring range: 175-200 mm



### Order data

Order number	420410 175-200
GTIN	2050001053138
Item class	43A

### Description

#### Version:

#### Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle.

Locking by clamping lever.

With ratchet and hand temperature protection.

With clearly engraved, black divisions and numerals.

#### Supplied with:

From size 25-50 including 1 setting standard.

Packaging: sturdy box

Standard: DIN 863

Micrometer barrel graduations: 1/50 mm

Calibration: B1

Calibration: B2

Scale divisions: 0.01 mm

Error limit: 7  $\mu$ m

Spindle  $\varnothing$ : 6.5 mm

Barrel  $\varnothing$ : 17.5 mm

### Technical description

Barrel $\varnothing$	17.5 mm
Micrometer barrel graduations	1/50 mm
Measuring range	175 - 200 mm

Scale divisions	0.01 mm
Spindle Ø	6.5 mm
Calibration	B1
Calibration	B2
Error limit	7 µm
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

## Services

Labellinglaser-etched Type	018940
CalibrationMicrometer standard for external micrometer maximum nominal size 300 mm	022080 300
CalibrationExternal tube micrometer maximum measuring range 200 mm	022000 200