



Tee bolt (12.9.) single, Type: 1412160



Order data

| | |
|--------------|----------------|
| Order number | 375310 1412160 |
| GTIN | 4020772087326 |
| Item class | 35A |

Description

Version:

T-bolt, forged and rolled thread.

High-tensile design, strength class = 12.9.

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

| | |
|---------------------|----------|
| T-slot nominal size | 14 mm |
| Height k | 8 mm |
| Thread length b | 100 mm |
| narrow nut width a | 13.7 mm |
| Nut width e | 22 mm |
| Thread G | M12 |
| Length L | 160 mm |
| Type | 787 |
| Type of product | Tee-bolt |

