

**Tee bolt (12.9.) single, Type: 1616125****Order data**

Order number	375310 1616125
GTIN	4020772087364
Item class	35A

Description**Version:**

T-bolt, forged and rolled thread.

High-tensile design, strength class = 12.9.

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

Thread length b	85 mm
narrow nut width a	15.7 mm
T-slot nominal size	16 mm
Height k	9 mm
Nut width e	25 mm
Thread G	M16
Length L	125 mm
Type	787
Type of product	Tee-bolt

