

Hartig**Precision external micrometer with 50 mm spindle travel, Measuring range: 250-300mm****Order data**

Order number	420900 250-300
GTIN	4250099609233
Item class	46P

Description**Version:**

Stable spheroidal cast frame, hammer finish with hand temperature protection, friction clutch, and locking device. Precision lapped, carbide-tipped measuring faces. Accuracy better than DIN 863.

Advantage:

50 mm spindle travel, ideal for larger measurement ranges. Direct reading of the 1/100 mm on the large scale barrel.

Supplied with:

Without setting standard.

Technical description

Micrometer barrel graduations	1/100 mm
Measuring range	250 - 300 mm
Spindle Ø	8 mm
Barrel Ø	24 mm
Scale divisions	0.01 mm
Calibration	B1
Error limit	5 µm
Standard	Manufacturer's standard

Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer without setting dimension maximum measuring range 300 mm	022000 300
DAkkS calibration External micrometer without setting dimension maximum measuring range 500 mm	022010 500