



Tee bolt (12.9.) single, Type: 2020315



Order data

Order number	375310 2020315
GTIN	4020772086459
Item class	35A

Description

Version:

T-bolt, forged and rolled thread.

High-tensile design, strength class = 12.9.

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

Height k	12 mm
Thread length b	190 mm
narrow nut width a	19.7 mm
T-slot nominal size	20 mm
Nut width e	32 mm
Thread G	M20
Length L	315 mm
Type	787
Type of product	Tee-bolt

