

Hartig

Large precision external micrometer with rear anvil extension, Measuring range: 200-300mm**Order data**

Order number	420920 200-300
GTIN	4250099610796
Item class	46P

Description**Version:**

Stable light metal cast frame, hammer finish with hand temperature protection, friction clutch, and locking device. Precision lapped, carbide-tipped measuring faces. Accuracy better than DIN 863. The screw-on rear anvil extension is lapped and carbide-tipped; it doubles the measuring range. Inner scale sleeve with scales for both measurement ranges.

Advantage:

Very large measuring range. After the rear anvil extension has been fitted, the micrometer is immediately ready for use. No additional setting block required. Direct reading of the 1/100 mm on the large scale barrel.

Supplied with:

Micrometer with 1 rear anvil extension. Without setting standard.

Note:

Versions up to 2000 mm measurement range available on request.
Special versions on request.

Technical description

Scale divisions	0.01 mm
Weight	3.8 kg
Barrel Ø	24 mm
Spindle Ø	10 mm

Measuring range	200 - 300 mm
Micrometer barrel graduations	1/100 mm
Spindle travel	50 mm
Calibration	S3
Error limit	6 µm
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometers with extensions Measuring range 200-300 mm	020450 200-300
--	----------------