

**Mitutoyo**
**Digital external micrometer IP65, Measuring range: 25-50mm**

**Order data**

Order number	421515 25-50
GTIN	4946368672915
Item class	44A

**Description**
**Version:**

Error limits more accurate than the requirements of **DIN 863**.

Extra large LCD display (7.5 mm high) for quick, error-free reading, keyboard lock.

Carbide-tipped measuring faces.

**Shock-proof version.**

Measuring spindle hardened and ground.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size 357, 1 setting standard from size 25 -50.

**Optional extras:**

No. 421525 and 421527. Data cable No. 497445.

**Technical description**

Measuring range	25 - 50 mm
Spindle pitch	0.5 mm
Spindle Ø	6.35 mm
Error limit	2 µm
Scale divisions	0.001 mm
Calibration	B1

Calibration	B2
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

### Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

### Accessories

Button cell / special battery Battery type 357	081560 357
Micrometer setting standard overall length 25 mm	421100 25