

Hartig

Large precision external micrometer with rear anvil extension, Measuring range: 500-600mm**Order data**

| | |
|--------------|----------------|
| Order number | 420920 500-600 |
| GTIN | 4250099610826 |
| Item class | 46P |

Description**Version:**

Stable light metal cast frame, hammer finish with hand temperature protection, friction clutch, and locking device. Precision lapped, carbide-tipped measuring faces. Accuracy better than DIN 863. The screw-on rear anvil extension is lapped and carbide-tipped; it doubles the measuring range. Inner scale sleeve with scales for both measurement ranges.

Advantage:

Very large measuring range. After the rear anvil extension has been fitted, the micrometer is immediately ready for use. No additional setting block required. Direct reading of the 1/100 mm on the large scale barrel.

Supplied with:

Micrometer with 1 rear anvil extension. Without setting standard.

Note:

Versions up to 2000 mm measurement range available on request.
Special versions on request.

Technical description

| | |
|-------------------------------|----------|
| Weight | 7.2 kg |
| Micrometer barrel graduations | 1/100 mm |
| Scale divisions | 0.01 mm |
| Spindle Ø | 10 mm |

| | |
|------------------------|--------------------------|
| Barrel Ø | 24 mm |
| Measuring range | 500 - 600 mm |
| Spindle travel | 50 mm |
| Calibration | S3 |
| Error limit | 9 µm |
| Standard | Manufacturer's standard |
| Measurement technology | analogue |
| Packaging | sturdy box |
| Type of product | External tube micrometer |

Services

| | |
|--|----------------|
| Calibration External micrometers with extensions Measuring range 500-600 mm | 020450 500-600 |
|--|----------------|