

Hartig

Large precision external micrometer with rear anvil extension, Measuring range: 600-700mm**Order data**

Order number	420920 600-700
GTIN	4250099610833
Item class	46P

Description**Version:**

Stable light metal cast frame, hammer finish with hand temperature protection, friction clutch, and locking device. Precision lapped, carbide-tipped measuring faces. Accuracy better than DIN 863. The screw-on rear anvil extension is lapped and carbide-tipped; it doubles the measuring range. Inner scale sleeve with scales for both measurement ranges.

Advantage:

Very large measuring range. After the rear anvil extension has been fitted, the micrometer is immediately ready for use. No additional setting block required. Direct reading of the 1/100 mm on the large scale barrel.

Supplied with:

Micrometer with 1 rear anvil extension. Without setting standard.

Note:

Versions up to 2000 mm measurement range available on request.
Special versions on request.

Technical description

Micrometer barrel graduations	1/100 mm
Spindle travel	50 mm
Weight	10 kg
Scale divisions	0.01 mm

Spindle Ø	10 mm
Barrel Ø	24 mm
Measuring range	600 - 700 mm
Calibration	S3
Error limit	9 µm
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometers with extensions Measuring range 600-700 mm	020450 600-700
--	----------------