

Mitutoyo**Digital external micrometer IP65, Measuring range: 75-100mm****Order data**

Order number	421515 75-100
GTIN	4946368672939
Item class	44A

Description**Version:**

Error limits more accurate than the requirements of **DIN 863**.

Extra large LCD display (7.5 mm high) for quick, error-free reading, keyboard lock.

Carbide-tipped measuring faces.

Shock-proof version.

Measuring spindle hardened and ground.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357, 1 setting standard from size 25 -50.

Optional extras:

No. 421525 and 421527. Data cable No. 497445.

Technical description

Spindle Ø	6.35 mm
Measuring range	75 - 100 mm
Spindle pitch	0.5 mm
Error limit	3 µm
Scale divisions	0.001 mm
Calibration	B1

Calibration	B2
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Button cell / special battery Battery type 357	081560 357
Micrometer setting standard overall length 75 mm	421100 75