



## Tee bolt (12.9.) single, Type: 202080



### Order data

Order number	375310 202080
GTIN	4020772086428
Item class	35A

### Description

#### Version:

T-bolt, forged and rolled thread.

**High-tensile design**, strength class = 12.9.

#### Standard:

**DIN 787**

#### Supplied with:

**Single**, without nut and washer.

#### Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

#### Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

### Technical description

narrow nut width a	19.7 mm
Height k	12 mm
T-slot nominal size	20 mm
Thread length b	55 mm
Nut width e	32 mm
Thread G	M20
Length L	80 mm
Type	787
Type of product	Tee-bolt

