



## External micrometer 1/100 graduations, Measuring range: 50-75mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 420750 50-75  |
| GTIN         | 4045197203878 |
| Item class   | 42B           |

### Description

#### Version:

#### Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle; with locking lever  
With ratchet and hand temperature protection.

#### Supplied with:

From size 25 – 50 supplied with 1 setting standard.

### Technical description

|                               |                          |
|-------------------------------|--------------------------|
| Barrel Ø                      | 30 mm                    |
| Scale divisions               | 0.01 mm                  |
| Spindle Ø                     | 8 mm                     |
| Measuring range               | 50 - 75 mm               |
| Micrometer barrel graduations | 1/100 mm                 |
| Calibration                   | B2                       |
| Standard                      | DIN 863                  |
| Measurement technology        | analogue                 |
| Packaging                     | sturdy box               |
| Type of product               | External tube micrometer |

---

## Services

DAkkS calibration External micrometer including setting  
dimension maximum measuring range 100 mm

022050 100

Calibration External micrometer including setting  
dimension maximum measuring range 100 mm

022040 100

---

## Accessories

Micrometer setting standard overall length 50 mm

421100 50