

Hartig

Precision external micrometer with 50 mm spindle travel, Measuring range: 200-250mm



Order data

Order number	420900 200-250
GTIN	4250099609226
Item class	46P

Description

Version:

Stable spheroidal cast frame, hammer finish with hand temperature protection, friction clutch, and locking device. Precision lapped, carbide-tipped measuring faces. Accuracy better than DIN 863.

Advantage:

50 mm spindle travel, ideal for larger measurement ranges. Direct reading of the 1/100 mm on the large scale barrel.

Supplied with:

Without setting standard.

Technical description

Micrometer barrel graduations	1/100 mm
Spindle Ø	8 mm
Barrel Ø	24 mm
Measuring range	200 - 250 mm
Scale divisions	0.01 mm
Calibration	B1
Error limit	5 µm
Standard	Manufacturer's standard

Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer without setting dimension maximum measuring range 300 mm	022000 300
DAkkS calibration External micrometer without setting dimension maximum measuring range 500 mm	022010 500