



External micrometer 1/100 graduations, Measuring range: 75-100mm



Order data

Order number	420750 75-100
GTIN	4045197203885
Item class	42B

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle; with locking lever
With ratchet and hand temperature protection.

Supplied with:

From size 25 – 50 supplied with 1 setting standard.

Technical description

Micrometer barrel graduations	1/100 mm
Measuring range	75 - 100 mm
Spindle Ø	8 mm
Scale divisions	0.01 mm
Barrel Ø	30 mm
Calibration	B2
Standard	DIN 863
Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting
dimension maximum measuring range 100 mm

022040 100

DAkkS calibration External micrometer including setting
dimension maximum measuring range 100 mm

022050 100

Accessories

Micrometer setting standard overall length 75 mm

421100 75