

**Garant****ZeroClamp 6-pot base plate or clamping towers for horizontal machines,  
Type: 10397****Order data**

|              |              |
|--------------|--------------|
| Order number | 360022 10397 |
| GTIN         |              |
| Item class   | 310          |

**Description****Version:**

Clamping pot  $\varnothing$  **120 mm**. The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

Clamping tower is mounted on base plate size 10243. Clamping towers are equipped laterally with clamping pots that can be individually activated and indexed.

**Optional extras:**

Clamping stud No. 360025.

**Technical description**

|         |        |
|---------|--------|
| Pitch S | 200 mm |
|---------|--------|

|                         |           |
|-------------------------|-----------|
| Type                    | 10397     |
| Number of clamping pots | 12        |
| Series                  | ZeroClamp |
| Indexing hole available | yes       |
| Type of product         | Baseplate |

## Accessories

|   |                  |
|---|------------------|
| ZeroClamp clamping stud with internal thread Type 12M10/90  | 360025 12M10/90  |
| ZeroClamp clamping stud with internal thread Type 16M8      | 360025 16M8      |
| ZeroClamp clamping stud with internal thread Type 16M10     | 360025 16M10     |
| ZeroClamp clamping stud with internal thread Type 25M10/138 | 360025 25M10/138 |
| ZeroClamp clamping stud with internal thread Type 12M10/138 | 360025 12M10/138 |
| ZeroClamp clamping stud with internal thread Type 25M16/138 | 360025 25M16/138 |
| ZeroClamp clamping stud with internal thread Type 14M12/90  | 360025 14M12/90  |
| ZeroClamp clamping stud with internal thread Type 12M10     | 360025 12M10     |
| ZeroClamp clamping stud with internal thread Type 18M12     | 360025 18M12     |
| ZeroClamp clamping stud with internal thread Type 18M12/138 | 360025 18M12/138 |
| ZeroClamp clamping stud with internal thread Type 18M16/138 | 360025 18M16/138 |
| ZeroClamp clamping stud with internal thread Type 18M16     | 360025 18M16     |
| ZeroClamp clamping stud with internal thread Type 25M10     | 360025 25M10     |