



## Tee bolt (12.9.) single, Type: 2824160



### Order data

|              |                |
|--------------|----------------|
| Order number | 375310 2824160 |
| GTIN         | 4020772086398  |
| Item class   | 35A            |

### Description

**Version:**

T-bolt, forged and rolled thread.

**High-tensile design**, strength class = 12.9.

**Standard:**

**DIN 787**

**Supplied with:**

**Single**, without nut and washer.

**Optional extras:**

Washers, see No. 375340 and tall nuts, see No. 375385.

**Note:**

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

### Technical description

|                     |          |
|---------------------|----------|
| T-slot nominal size | 28 mm    |
| narrow nut width a  | 27.7 mm  |
| Thread length b     | 110 mm   |
| Height k            | 18 mm    |
| Nut width e         | 44 mm    |
| Thread G            | M24      |
| Length L            | 160 mm   |
| Type                | 787      |
| Type of product     | Tee-bolt |

