



Tee bolt (12.9.) single, Type: 2824400



Order data

Order number	375310 2824400
GTIN	4020772086411
Item class	35A

Description

Version:

T-bolt, forged and rolled thread.

High-tensile design, strength class = 12.9.

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 375340 and tall nuts, see No. 375385.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

Nut width e	44 mm
Thread length b	240 mm
T-slot nominal size	28 mm
Height k	18 mm
narrow nut width a	27.7 mm
Thread G	M24
Length L	400 mm
Type	787
Type of product	Tee-bolt

