

Garant**ZeroClamp clamping stud with internal thread, Type: 14M12/90****Order data**

Order number	360025 14M12/90
GTIN	4045197518774
Item class	310

Description**Version:**

With internal thread including a suitable threaded pin. The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

Technical description

suitable for clamping pot Ø	90 mm
Centre Ø D	14 mm
Thread M ₂ external	M8
Thread M ₁ external	M12

Series	ZeroClamp
Tolerance external Ø	k6
Type of product	Clamping studs