


**T-nut with threaded shank, T-slot nominal size: 10mm****Order data**

Order number	375315 10
GTIN	4020772080020
Item class	35A

Description**Application:**

For combination with studs or bolts.

Standard:

DIN 508

Material:

Quenched and tempered steel, strength 10.

Note:

Full load-bearing capacity only when threaded for the **entire** nut length.

Technical description

Thread	M8
T-slot nominal size	10 mm
Nut height	12 mm
Width a	9.7 mm
Width e	15 mm
Height k	6 mm

Type	508
Type of product	Tee-nut