

**Rhombus T-bolt, T-slot nominal size×length L: 28X125mm****Order data**

| | |
|--------------|---------------|
| Order number | 375335 28X125 |
| GTIN | 4020772086954 |
| Item class | 35A |

Description**Version:**

- Forged and milled
- T-slots, rolled thread.
- Hardened to strength class 10.9.

Application:

Later insertion of an additional clamping point is made easier on long tables. The T-bolt is inserted into the T-slot from above.

Technical description

| | |
|---------------------|---------|
| Thread length b | 85 mm |
| Height k | 18 mm |
| Nut width e | 44 mm |
| T-slot nominal size | 28 mm |
| narrow nut width a | 27.7 mm |
| Thread G | M24 |

| | |
|-----------------|----------|
| Length L | 125 mm |
| Type | 797 |
| Rhombus | yes |
| Type of product | Tee-bolt |