

**T-nut with threaded shank, T-slot nominal size: 12mm****Order data**

Order number	375315 12
GTIN	2050002046993
Item class	35A

Description**Application:**

For combination with studs or bolts.

Standard:

DIN 508

Material:

Quenched and tempered steel, strength 10.

Note:

Full load-bearing capacity only when threaded for the **entire** nut length.

Technical description

Thread	M10
T-slot nominal size	12 mm
Nut height	14 mm
Width a	11.7 mm
Width e	18 mm
Height k	7 mm

Type	508
Type of product	Tee-nut

Accessories

T-nut for T-slot nominal size 12 mm	370530 12
-------------------------------------	-----------