

Garant**Try square stainless, accuracy class 0, Stock length: 50X40mm****Order data**

Order number	451020 50X40
GTIN	4045197443830
Item class	41G

Description**Version:**

Precision squares of stainless steel, fully hardened and stress relieved. Test faces ground and very precisely adjusted, all other faces ground.

Application:

For inspection and high precision work.

Accuracy:

DIN 875 / 0 – angle tolerance e.g. for size 100×70 = 0.007 mm.

Technical description

Right angle tolerance	0.007 mm
Shank cross-section	15×4 mm
Stock length	50×40 mm
Calibration	F1
Standard	DIN 875
Accuracy	0

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Try squares

Services

CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750