

Garant**Bevel try square hardened stainless, accuracy class 00, Stock length:
75X50mm****Order data**

Order number	450020 75X50
GTIN	4045197443984
Item class	41G

Description**Version:**

Very high accuracy. With two bevelled straight edges on the long blade.
Through hardened and stress-relieved. Test faces ground and lapped, other faces ground.

With sturdy stock.**Application:**

For inspection work using the light gap principle.

Technical description

Right angle tolerance	0.003 mm
Length of long arm	75 mm
Cross-section of long arm	18×3 mm
Cross-section of short arm	16×12 mm
Length of short arm	50 mm
Standard	DIN 875/00

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Calibration	F1
Type of product	Bevel square

Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100