

**Garant****Try square stainless, accuracy class 0, Stock length: 75X50mm****Order data**

Order number	451020 75X50
GTIN	4045197443847
Item class	41G

**Description****Version:**

Precision squares of stainless steel, fully hardened and stress relieved. Test faces ground and very precisely adjusted, all other faces ground.

**Application:**

For inspection and high precision work.

**Accuracy:**

**DIN 875 / 0** – angle tolerance e.g. for size 100×70 = 0.007 mm.

**Technical description**

Shank cross-section	15×4 mm
Right angle tolerance	0.007 mm
Stock length	75×50 mm
Calibration	F1
Standard	DIN 875
Accuracy	0

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Try squares

### Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100

### Accessories

Wooden case for stock length 75X50 mm	451600 75X50
---------------------------------------	--------------