

Mitutoyo
Digital external micrometer with offset measuring faces, Measuring range: 0-25mm


Order data

Order number	421610 0-25
GTIN	4946368688848
Item class	44A

Description

Version:

Clear (7.5 mm high), digital measured value display provides quick readings. Addition reading by vernier. Sintered, precision lapped, carbide tipped anvils, measuring spindle hardened and ground. Locking by clamping screw. Measuring force at the ratchet 5 - 10 N.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

From size 25-50 including 1 setting standard. 1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497445.

Technical description

Measuring range	0 - 25 mm
Calibration	B1
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	DIN 863

Interface	USB interface
Interface	Digimatic interface
Measurement technology	digital
Packaging	sturdy box
Type of product	External micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25

Accessories

Button cell / special battery Battery type 357	081560 357
Connecting cable with data switch Type D1	497445 D1
Transmitter Type S16E	498966 S16E
Receiver / USB keyboard interface Type	498965
Connecting cable with data switch Type USB2	497445 USB2
Connecting cable with data switch Type D2	497445 D2
Multi-receiver / USB keyboard interface Type	498975