


Stock square Accuracy class 2, Stock length: 100X70mm

Order data

Order number	452590 100X70
GTIN	4045197372123
Item class	42F

Description
Version:

All faces and edges ground. Inspection test faces ground.

Application:

For accurate general workshop work.

Accuracy:

DIN 875 / 2 – angle tolerance e.g. for size 100×70 = 0.030 mm.

Technical description

Right angle tolerance	0.03 mm
Shank cross-section	20×5 mm
Stock length	100×70 mm
Calibration	F1
Standard	DIN 875
Accuracy	2

Type of product

Stock square

ServicesDAkkS calibration
Stock, try, and bevel edge squares
maximum arm length 750 mm

025010 750

Calibration
Stock, try, and bevel edge squares maximum
arm length 100 mm

025000 100

Accessories

Wooden case for stock length 100X70 mm

451600 100X70