

**Garant****Bevel try square hardened stainless, accuracy class 00, Stock length: 150X100mm****Order data**

Order number	450020 150X100
GTIN	4045197444004
Item class	41G

**Description****Version:**

**Very high accuracy.** With two bevelled straight edges on the long blade. Through hardened and stress-relieved. Test faces ground and lapped, other faces ground.

**With sturdy stock.****Application:**

For inspection work using the light gap principle.

**Technical description**

Length of long arm	150 mm
Cross-section of short arm	22×12 mm
Cross-section of long arm	22×4 mm
Right angle tolerance	0.004 mm
Length of short arm	100 mm
Standard	DIN 875/00

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Calibration	F1
Type of product	Bevel square

## Services

CalibrationStock, try, and bevel edge squares maximum arm length 300 mm	025000 300
DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750