

Garant

Bevel edge square, flat version stainless, accuracy class 00, Stock length: 100X70mm

**Order data**

Order number	450010 100X70
GTIN	4045197443953
Item class	41G

Description**Version:**

Very high accuracy. With two bevelled straight edges on the long blade.
Through hardened and stress-relieved. Test faces ground and lapped, other faces ground.

Application:

For inspection work using the light gap principle.

Technical description

Shank cross-section	20×5 mm
Length of short arm	70 mm
Right angle tolerance	0.003 mm
Length of long arm	100 mm
Standard	DIN 875/00
Material	Stainless steel, INOX

all parts	hardened
Packaging	sturdy box
Calibration	F1
Type of product	Bevel square

Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 100 mm	025000 100