

**Stock square Accuracy class 2, Stock length: 150X100mm****Order data**

Order number	452590 150X100
GTIN	4045197372130
Item class	42F

**Description****Version:**

All faces and edges ground. Inspection test faces ground.

**Application:**

For accurate general workshop work.

**Accuracy:**

**DIN 875 / 2** – angle tolerance e.g. for size 100×70 = 0.030 mm.

**Technical description**

Shank cross-section	25×5 mm
Right angle tolerance	0.035 mm
Stock length	150×100 mm
Calibration	F1
Standard	DIN 875
Accuracy	2

Type of product

Stock square

**Services**

Calibration Stock, try, and bevel edge squares maximum arm length 300 mm

025000 300

DAkkS calibration Stock, try, and bevel edge squares maximum arm length 750 mm

025010 750

**Accessories**

Wooden case for stock length 150X100 mm

451600 150X100