

Garant**Stock square stainless, accuracy class 1, Stock length: 400X265mm****Order data**

Order number	451030 400X265
GTIN	4045197444141
Item class	41G

Description**Version:**

All faces and edges precision ground. Inspection test faces finish ground. Stock squares of stainless steel, fully hardened and stress relieved. Protective packaging for safe transport.

Application:

For inspection and high precision work.

Accuracy:

DIN 875 / 1 – angle tolerance e.g. for size 100×70 = 0.015 mm.

Technical description

Shank cross-section	45×10 mm
Right angle tolerance	0.03 mm
Stock length	400×265 mm
Calibration	F1
Standard	DIN 875
Accuracy	1

Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Stock square

Services

DAkkS calibrationStock, try, and bevel edge squares maximum arm length 750 mm	025010 750
CalibrationStock, try, and bevel edge squares maximum arm length 750 mm	025000 750

Accessories

Wooden case for stock length 400X265 mm	451600 400X265
---	----------------